





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISI

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	8/20/21	PHOSPODAR
B	UPDATE COMPONENT VIEWS	10/13/21	PHOSPODAR



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-com™ an INFINITe brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936			
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY DMAY	08/12/2021	CATEGORY		FIBER OPTICS			
	CHECKED BY PHOSPODAR	8/20/21						
	APPROVED BY PHOSPODAR	8/20/21						
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS .XX = ± .02 [5] ± 1/32 .XXX = ± .005 [13] ANGLES ± 1°	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY							
THIRD-ANGLE PROJECTION	PRODUCT DESCRIPTION FIBER OPTIC ECONOMY COUPLER, LC, AQUA, DUPLEX W/ SC FP MMF, PLASTIC BODY, PEI CLIP							
	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. FOA-LCM32-PC0N-SCF	REV. B			
	SCALE: NONE	CAD FILE: FOA-LCM32-PC0N-SCF.SLDDRW			SHEET 1 OF 1			

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)