



8 7 6 5 4 3 2 1
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|------------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 02/27/2020 | PHOSPODAR |
| | | | |
| | | | |
| | | | |



NOTES:


1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. LC CONNECTOR ASSEMBLY POLISH TYPE: PC
3. ALL CONNECTORS ACCCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
4. COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
 ≤ 12 [305] = $+1$ [25] / -0
 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
 > 300 [7620] = $+5%$ / -0

ALL OTHER DIMENSIONAL TOLERANCES:

$.X = \pm .2$ [5] FRACTIONS
 $.XX = \pm .02$ [.5] $\pm 1/32$
 $.XXX = \pm .005$ [.13] ANGLES $\pm 1^\circ$



APPROVALS

DATE

DRAWN BY

DFRISIELLO

02/27/2020

CHECKED BY

PHOSPODAR

02/25/2020

APPROVED BY

PHOSPODAR

02/25/2020

REV.

L-COMTM
an INFINIT^E brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

CATEGORY

FIBER OPTICS

PRODUCT DESCRIPTION

LC SIMPLEX MMF connector for 3.0mm fiber

SIZE

A

CAGE CODE

43321

ITEM NO.

FOC-LCMM30

REV.

A

SCALE:

NONE

CAD FILE: FOC-LCMM30.SLDDRW

SHEET 1 OF 1