


8 7 6 5 4 3 2 1  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/11/2020	PHOSPODAR



#### NOTES:

#### MATERIALS:

BODY: ZINC ALLOY, NICKEL PLATED

SLEEVE: ZIRCONIA

FC DUST CAP: VINYL, GREEN

SC DUST CAP: ENGINEERING PLASTIC, GREEN

MOUNTING CLIP: STAINLESS STEEL

FC CONNECTOR ASSEMBLY POLISH TYPE: APC  
SC CONNECTOR ASSEMBLY POLISH TYPE: APC

RECOMMENDED PANEL THICKNESS: .06" [1.5]

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

SHIPPED WITH DUST CAPS INSTALLED.

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</p> <p>OVERALL CABLE LENGTH TOLERANCE:  <math>\leq 12</math> [305] = +1 [25] / -0  <math>&gt; 12</math> [305] <math>\leq 60</math> [1524] = +2 [51] / -0  <math>&gt; 60</math> [1524] <math>\leq 120</math> [3048] = +4 [102] / -0  <math>&gt; 120</math> [3048] <math>\leq 300</math> [7620] = +6 [152] / -0  <math>&gt; 300</math> [7620] = +8% / -0         </p> <p>ALL OTHER DIMENSIONAL TOLERANCES:  <math>.X = \pm .2</math> [5]  <math>.XX = \pm .02</math> [5]  <math>.XXX = \pm .005</math> [1.3]         </p> <p>THIRD-ANGLE PROJECTION</p>	APPROVALS	DATE	<p><b>L-com</b> an INFINITE brand</p> <p>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</p> <p>CATEGORY</p> <p>FIBER OPTICS</p>
	DRAWN BY DFRISIELLO	08/11/2020	
	CHECKED BY PHOSPODAR	08/11/2020	
	APPROVED BY PHOSPODAR	08/11/2020	
<p>CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY</p> <p>COLOR VARIATIONS MAY OCCUR</p>	SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>FOA-SM-FCAFSCAF-R</b>
	SCALE: NONE	CAD FILE: FOA-SM-FCAFSCAF-R.SLDDRW	REV. <b>A</b>
			SHEET 1 OF 1