




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/22/2021	PHOSPODAR

WIRING MAP TYPE A		
J1	COLOR	J2
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5		5
6		6
7		7
8		8
9	YELLOW	9
10	PURPLE	10
11	ROSE	11
12	AQUA	12



LENGTH	
ITEM NO.	METERS [FEET]
MPFF8SMAR-1	1.0 [3.28]
MPFF8SMAR-3	3.0 [9.84]
MPFF8SMAR-5	5.0 [16.40]
MPFF8SMAR-10	10.0 [32.81]

<div>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]</div> <div>OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0</div> <div>ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]</div> <div>THIRD-ANGLE PROJECTION</div> <div></div>	APPROVALS	DATE	<div></div> <div>50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936</div>	
	DRAWN BY DZINN	10/22/2021		CATEGORY
	CHECKED BY DFRISIELLO	10/22/2021		
	APPROVED BY PHOSPODAR	10/22/2021		
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		FIBER OPTICS		
PRODUCT DESCRIPTION		Fiber patch cable MPO female to MPO female, 8 fiber SMF type A, OFNR rated		
SIZE A	CAGE CODE 43321	ITEM NO. MPFF8SMAR	REV. A	
SCALE: NONE		CAD FILE: MPFF8SMAR.SLDDRW		
		SHEET 1 OF 1		