


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/19/2021	PHOSPODAR

WIRING MAP				
J1	COLOR	J2	J3	J4
1	BLUE	12		
2	ORANGE	11		
3	GREEN	10		
4	BROWN	9		
5	GRAY		12	
6	WHITE		11	
7	RED		10	
8	BLACK		9	
9	YELLOW			12
10	PURPLE			11
11	ROSE			10
12	AQUA			9
13	BLUE w/TRACER	4		
14	ORANGE w/TRACER	3		
15	GREEN w/TRACER	2		
16	BROWN w/TRACER	1		
17	GRAY w/TRACER		4	
18	WHITE w/TRACER		3	
19	RED w/TRACER		2	
20	BLACK w/TRACER		1	
21	YELLOW w/TRACER			4
22	PURPLE w/TRACER			3
23	ROSE w/TRACER			2
24	AQUA w/TRACER			1



PART NUMBER	METERS (FEET)
MPF24308SMR-1	1.0 (3.28)
MPF24308SMR-3	3.0 (9.84)
MPF24308SMR-5	5.0 (16.40)
MPF24308SMR-10	10.0 (32.81)

- NOTES:
1. MPO CONNECTOR SINGLE MODE ASSEMBLY POLISH TYPE: APC
 2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
 3. PACKAGING: INDIVIDUALLY PACKAGE EACH ASSEMBLY IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13]	APPROVALS DRAWN BY: DZINN CHECKED BY: DFRISIELLO APPROVED BY: PHOSPODAR	DATE 03/19/2021 03/19/2021 03/19/2021		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY COLOR VARIATIONS MAY OCCUR		PRODUCT DESCRIPTION FIBER CONV HARNESS, MPO24 (F) TO 3XMPO8 (F)
SIZE A		CAGE CODE 43321	ITEM NO. MPF24308SMR	REV. A
SCALE: NONE		CAD FILE: MPF24308SMR.SLDDRW		SHEET 1 OF 1