




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/22/2021	PHOSPODAR

WIRING MAP TYPE A		
J1	COLOR	J2
1	BLUE	1
2	ORANGE	2
3	GREEN	3
4	BROWN	4
5		5
6		6
7		7
8		8
9	YELLOW	9
10	PURPLE	10
11	ROSE	11
12	AQUA	12



LENGTH	
ITEM NO.	METERS [FEET]
MPFF8SMAZ-1	1.0 [3.28]
MPFF8SMAZ-3	3.0 [9.84]
MPFF8SMAZ-5	5.0 [16.40]
MPFF8SMAZ-10	10.0 [32.81]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]             FRACTIONS .XX = ± .02 [.5]           ± 1/32 .XXX = ± .005 [.13]        ANGLES ± 1°  THIRD-ANGLE PROJECTION  	APPROVALS	DATE	 <div>50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936</div>			
	DRAWN BY DZINN	10/22/2021			CATEGORY	
	CHECKED BY DFRISIELLO	10/22/2021				
	APPROVED BY PHOSPODAR	10/22/2021				
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			PRODUCT DESCRIPTION  Fiber patch cable MPO female to MPO female, 8 fiber SMF type A, LSZH rated			
COLOR VARIATIONS MAY OCCUR			SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. <b>MPFF8SMAZ</b>	REV. <b>A</b>
			SCALE: NONE		CAD FILE: MPFF8SMAZ.SLDDRW	SHEET 1 OF 1