
REVISIONS				
REV.	DESCRIPTION	DATE	APPROVED	
Α	INITIAL RELEASE	02-08-2021	PHOSPODAR	



PART NUMBER	LENGTH Meters [feet]	
FOA6ODD8-001M	1.0 [3.28]	
FOA6ODD8-002M	2.0 [6.56]	
FOA6ODD8-005M	5.0 [16.40]	
FOA6ODD8-010M	10.0 [32.80]	
FOA6ODD8-012M	12.0 [39.37]	

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

 $.X = \pm .2$ [5.08] FRACTIONS $.XX = \pm .02$ [.51] ± 1/32 .XXX = ±.005 [.13] | ANGLES ± 1°

CABLE LENGTH (L) TOLERANCES:

L ≤ 12 [305] = +1 [25] / -0 12 [305] < L ≤ 60 [1524] = +2 [51] / -0 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 300 [7620] < L = +5%L / -0

> ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.



50 High Street, West Mill, 3rd Floor, Suite #30 North Andover, MA 01845 USA.

Phone: 1.800.341.5266 | 1.978.682.6936 Fax: 1.978.689.9484 Website: www.L-com.com

E-mail: CustomerService@L-com.com

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF L-COM GLOBAL CONNECTIVITY ALL RIGHTS RESERVED.

THIRD-ANGLE PROJECTION

Α

N/A SIZE CAGE CODE DRAWN BY ITEM NO. REV 43321 MVEERAPPAN FOA6ODD8

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.