


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|------------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 08/11/2021 | PHOSPODAR |
| | | | |
| | | | |





| ITEM NO. | LENGTH | |
|-------------------|--------|-------|
| | METER | FEET |
| FCA-LCLC-DPM1P-01 | 1.0 | 3.28 |
| FCA-LCLC-DPM1P-02 | 2.0 | 6.56 |
| FCA-LCLC-DPM1P-03 | 3.0 | 9.84 |
| FCA-LCLC-DPM1P-05 | 5.0 | 16.40 |
| FCA-LCLC-DPM1P-10 | 10.0 | 32.81 |
| FCA-LCLC-DPM1P-15 | 15.0 | 49.21 |

NOTES:

- LC CONNECTOR POLISH TYPE: UPC.
- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

| | | | |
|--|--|---------------------------------|---|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] | APPROVALS | DATE |  an INFINITI brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 |
| | DRAWN BY DZINN | 08/11/2021 | |
| | CHECKED BY DFRISIELLO | 08/11/2021 | |
| | APPROVED BY PHOSPODAR | 08/11/2021 | |
| THIRD-ANGLE PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | CATEGORY FIBER OPTICS |
| | COLOR VARIATIONS MAY OCCUR | | PRODUCT DESCRIPTION FIBER OPTIC PATCH CABLE LC TO LC DUPLEX 62.5/125 MULTIMODE OM1 OFNP |
| | SIZE A | CAGE CODE 43321 | ITEM NO. FCA-LCLC-DPM1P |
| SCALE: NONE | | CAD FILE: FCA-LCLC-DPM1P.SLDDRW | REV. A |