



8 7 6 5 4 3 2 1  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/10/2020	PHOSPODAR



#### NOTES:

#### MATERIALS:

HOUSING: ABS THERMOPLASTIC, BLACK

DUST CAPS: VINYL, BLACK

DUST CAP (REAR): DIE-CAST ZINC, BLACK

MALE SC CONNECTOR ASSEMBLY POLISH TYPE: PC  
FEMALE SC CONNECTOR ASSEMBLY POLISH TYPE: PC

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED.

COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:  
 $\leq 12$  [305] =  $+1$  [25] / -0  
 $> 12$  [305]  $\leq 60$  [1524] =  $+2$  [51] / -0  
 $> 60$  [1524]  $\leq 120$  [3048] =  $+4$  [102] / -0  
 $> 120$  [3048]  $\leq 300$  [7620] =  $+6$  [152] / -0  
 $> 300$  [7620] =  $+5%$  / -0

ALL OTHER DIMENSIONAL TOLERANCES:  
 $.X = \pm .2$  [5]      FRACTIONS  
 $.XX = \pm .02$  [.5]       $\pm 1/32$   
 $.XXX = \pm .005$  [.13]      ANGLES  $\pm 1^\circ$



APPROVALS  
DRAWN BY  
DFRISIELLO

DATE  
08/06/2020  
CHECKED BY  
PHOSPODAR

APPROVED BY  
PHOSPODAR

08/10/2020

**L-COM**<sup>TM</sup>  
an INFINITE brand

50 High Street, West Mill,  
North Andover, MA 01845 USA.  
Phone: 1.800.341.5266  
1.978.682.6936

CATEGORY

FIBER OPTICS

PRODUCT DESCRIPTION

SC Buffered Fiber Adapter for 900um fiber

SIZE      CAGE CODE      ITEM NO.  
**A**      **43321**      **FOA-SCB9**

REV.      SHEET 1 OF 1  
**A**