

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


| REVISIONS | | | |
|-----------|------------------------------|---------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | DRAWING REPLACES FOA-702-OD1 | 9/24/14 | D. CASTRO |
| . | . | . | . |
| . | . | . | . |
| . | . | . | . |

D

C



B

A



2X ZIRCONIA SLEEVE

2X MU DUPLEX ADAPTOR





RECOMMENDED
PANEL OPENING

NOTES:

1. SHIPPED WITH DUST CAPS INSTALLED (NOT SHOWN).
2. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
3. RECOMMENDED PANEL THICKNESS: 0.06"

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

| | | | | |
|--|--|--------------------------|---|--------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13] | APPROVALS | DATE |  45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | |
| | DRAWN BY MCCORMICK | 10/24/02 | | |
| | CHECKED BY D.PARHAM | 10/24/02 | CATEGORY FIBER OPTICS | |
| | APPROVED BY R.CARRICK | 10/24/02 | PRODUCT DESCRIPTION MU-MU DUPLEX COUPLER | |
| PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | SIZE A | FSCM NO. 43321 |
| COLOR VARIATIONS MAY OCCUR | | DWG. NO. FOA-702 | REV. A | |
| SCALE: NONE | | CAD FILE: FOA-702.SLDDRW | | SHEET 1 OF 1 |