


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISONS

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/15/11	D.GRIFFIN
B	ECN 5402: REMOVE "PS-0031" FROM PACKAGING NOTE	3/22/11	D.FRISIELLO



NOTES:

ALL DIMENSIONS ARE FOR REFERENCE ONLY.

A COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATIONS.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	L-COM [®] Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
OVERALL CABLE LENGTH TOLERANCE: <12 [305] = +1 [25] / -0 >12 [305] <60 [1524] = +2 [51] / -0 >60 [1524] <120 [3048] = +4 [102] / -0 >120 [3048] <300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	DRAWN BY D.FRISIELLO	3/8/11	
ALL OTHER DIMENSIONAL TOLERANCES: $X = \pm .2$ $XX = \pm .02$ $XXX = \pm .005$	CHECKED BY K.BURGNER	3/8/11	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY COAXIAL		
PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
		DWG. NO. SC2402RTM	REV. B
	SCALE: NONE	CAD FILE: SC2402RTM.SLDDRW	SHEET 1 OF 1