




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	9/22/11	D.GRIFFIN
B	ECN 6563: UPDATED TOLERANCE FOR 4M AND 5M. UPDATED CONNECTOR MODEL	12/4/12	D. DESJARDIN
C	ECN 7303: REMOVED COLORS FROM WIRE MAP, ADDED REGULATORY	2/20/14	D. CASTRO



UL20276
 (4) 30AWG INDIVIDUALLY SHIELDED TWISTED PAIRS,
 (1) 30AWG UNSHIELDED TWISTED PAIR,
 (5) 30AWG INDIVIDUAL CONDUCTORS,
 OVERALL SHIELD: ALUMINUM MYLAR FOIL SHIELD PLUS
 COPPER BRAID SHIELD WITH DRAIN WIRE,
 OUTER JACKET: PVC, BLACK

PART NUMBER	LENGTH	
	MM	INCHES
SWHD-1	1000 +75/-0	39.4 +2.95/-0
SWHD-2	2000 +75/-0	78.7 +2.95/-0
SWHD-3	3000 +75/-0	118.1 +2.95/-0
SWHD-4	4000 +150/-0	157.5 +5.91/-0
SWHD-5	5000 +150/-0	196.8 +5.91/-0



- NOTES:**
1. CABLE IS SHIPPED WITH (2) DUST COVERS INSTALLED (NOT SHOWN).
 2. CABLE SHALL BE TESTED FOR CONTINUITY.
 3. CABLE SHALL BE PACKAGED PER L-COM PACKAGING SPEC PS-0031.

REGULATORY COMPLIANCE:
 CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. CASTRO	9/21/11		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [1.51] .XXX = ± .005 [1.13]	CHECKED BY D. PARHAM	9/21/11	PRODUCT DESCRIPTION	CBL HDMI SWIVEL CON
PROJECTION 	APPROVED BY P. MCNEIL	9/21/11	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
	COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321
			DWG. NO. SWHD	REV. C
			SCALE: NONE	CAD FILE: SWHD.SLDRW
				SHEET 1 OF 1