





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
E	ECN 10265: REVISED MATERIAL OF MTG PLATE TO STEEL, NICKEL PLATED	12/16/2019	BGATES




- NOTES:
1. MATERIAL: HOUSING; CAST ALUMINUM. INSULATOR; GLASS FILLED PBT (BLUE) U.L. 94V-0 FLAMMABILITY RATING.
  2. MOUNTING FLANGE: STEEL, NICKEL PLATED.
  3. FINISH: HOUSING; NICKEL PLATED. CONTACTS; 15 MICRO INCHES GOLD PLATE.
  4. WIRING: STRAIGHT THRU.
  5. TWO DUST CAPS PROVIDED WITH ADAPTOR.
  6. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
EU ROHS DIRECTIVE (MOST RECENT RELEASED VERSION)



DETAIL A: INTERNAL THREAD DEPTH

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm].		APPROVALS		DATE		 an INFINITI brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE:		DRAWN BY R.CARRICK		08/17/2001		IEEE-488		CATEGORY  IEEE-488	
<12 [305] = +1 [25] / -0		CHECKED BY D.FAIRBANK		08/27/2001					
>12 [305] <60 [1524] = +2 [51] / -0		APPROVED BY C.MACCORRICK		08/27/2001					
>60 [1524] <120 [3048] = +4 [102] / -0									
>120 [3048] <300 [7620] = +6 [153] / -0									
>300 [7620] = +5% / -0									
ALL OTHER DIMENSIONAL TOLERANCES:		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION		IEEE-488 BULKHEAD ADAPTOR, FEMALE-FEMALE			
.X = $\pm .2$ [5] FRACTIONS		COLOR VARIATIONS MAY OCCUR		SIZE		CAGE CODE		DWG. NO.	
.XX = $\pm .02$ [1.3] FRACTIONS				B		43321		CIB24BF	
.XXX = $\pm .005$ [1.3] FRACTIONS				SCALE: NONE		CAD FILE: CIB24BF.SLDRAW		SHEET 1 OF 1	
THIRD-ANGLE PROJECTION									
