


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|---------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 6/28/11 | D.GRIFFIN |
| | | | |
| | | | |



| WIRING MAP | | | |
|------------|-------|-------|-------|
| "P1" | "J1" | "P1" | "J2" |
| 1 | 1 | 1 | 1 |
| 2 | 2 | 2 | 2 |
| 3 | 3 | 3 | 3 |
| 4 | 4 | 4 | 4 |
| 5 | 5 | 5 | 5 |
| 6 | 6 | 6 | 6 |
| 7 | 7 | 7 | 7 |
| 8 | 8 | 8 | 8 |
| 9 | 9 | 9 | 9 |
| 10 | 10 | 10 | 10 |
| 11 | 11 | 11 | 11 |
| 12 | 12 | 12 | 12 |
| 13 | 13 | 13 | 13 |
| 14 | 14 | 14 | 14 |
| 15 | 15 | 15 | 15 |
| SHELL | SHELL | SHELL | SHELL |

- NOTE:
1. ADAPTER SHALL BE TESTED FOR CONTINUITY.
 2. ADAPTER SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
 3. D-SUB PIN PLATING: 30 microns GOLD

| | | | | |
|--|--|--|--|-----------------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 | APPROVALS DRAWN BY D. PARHAM CHECKED BY D. CASTRO APPROVED BY S. SMITH | DATE 02/14/2011 02/18/2011 02/18/2011 | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | |
| | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | CATEGORY D-SUB | |
| | PROJECTION | COLOR VARIATIONS MAY OCCUR | PRODUCT DESCRIPTION DB15M/2-DB15F WYE | SIZE A |
| | FSCM NO. 43321 | DWG. NO. ADPT-DB15Y | SCALE: NONE | CAD FILE: ADPT-DB15Y.SLDDRW |
| SHEET 1 OF 1 | | | REV. A | |