

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	07/02/01	MCCORMICK
B	REVISED; ADDED THREAD CALLOUT AND PANEL OPENING	03/25/02	MCCORMICK
C	ECN 3124: UPDATE DWG FORMAT	12/19/07	D.GRIFFIN
D	ECN 5950: REVISED PER VENDOR SPECIFICATIONS, NEW FORMAT	2/1/12	D.FRISIELLO


DESCRIPTION	MATERIAL	FINISH
BODY	BRASS	NICKEL PLATE
DIELECTRIC	TEFLON	-
CENTER CONTACT	BRASS	GOLD PLATE
LOCK WASHER	BRASS	NICKEL PLATE
NUT	BRASS	NICKEL PLATE
WATERPROOF SEAL	RUBBER	-

D

C

B

A



NOTES:

ELECTRICAL:
 IMPEDANCE: 50 OHMS
 FREQUENCY RANGE: DC ~ 6 GHz
 VOLTAGE RATING: 500 VOLTS PEAK
 DIELECTRIC WITHSTANDING VOLTAGE: 1000V RMS
 INSERTION LOSS: .15dB MAX.

MISCELLANEOUS:
 ALL DIMENSIONS ARE FOR REFERENCE ONLY.

COMPONENTS SHALL BE INDIVIDUALLY PACKAGED
 IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

RECOMMENDED
 PANEL OPENING

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY MCCORMICK	06/13/01		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D.PARHAM	07/02/01	CATEGORY COAXIAL	
	APPROVED BY ENG	07/02/01	PRODUCT DESCRIPTION SMA JACK BULKHEAD ADAPTOR	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
REF			DWG. NO. BA21	REV. D
			SCALE: NONE	CAD FILE: BA21.SLDDRW
				SHEET 1 OF 1

8

7

6

5

4

3

2

1