





Pin数	尺寸A	尺寸B	尺寸C
2×3	5.08	13.22	15.22
2×4	7.62	15.76	17.76
2×5	10.16	18.30	20.30
2×6	12.70	20.84	22.84
2×7	15.24	23.38	25.38
2×8	17.78	25.92	27.92
2×9	20.32	28.46	30.46
2×10	22.86	31.0	33.00
2×11	25.40	33.82	35.54
2×12	27.94	36.36	38.08
2×13	30.48	38.62	40.62
2×14	33.02	41.16	43.16
2×15	35.56	43.70	45.70
2×16	38.10	46.24	48.24
2×17	40.64	48.78	50.78
2×18	43.18	51.32	53.32
2×19	45.72	53.86	55.86
2×20	48.26	56.4	58.40
2×21	50.80	58.94	60.94
2×22	53.34	61.48	63.48
2×23	55.88	64.02	66.02
2×24	58.42	66.56	68.56
2×25	60.96	69.10	71.10
2×26	63.50	71.64	73.64
2×27	66.04	74.18	76.18
2×28	68.58	76.72	78.72
2×29	71.12	79.26	81.26
2×30	73.66	81.80	83.80
2×31	76.20	84.34	86.34
2×32	78.74	86.88	88.88



技术规范:  
 额定电流 : 3AMP  
 适用温度 : -40°Cto+105°C  
 接触电阻 : 20mΩ Max  
 绝缘电阻 : 1000MΩ Min  
 耐电压 : AC 1000V  
 绝缘材料 : PA9T  
 端子材质 : Brass  
 电镀规范 : Au G/F

new		2015/5/3	A	瀚源	
ECN BO.		DATE.	REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2	SCALE: 3:1
Mikey	Tom	Jerry	PART NAME HY2541WR-N-2xXXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3
			MODEL NAME HY2541WR-N-2xXXP		3RD ANGLE PROJ
				FILE.NO.	