




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	ECR-22-157618		07NOV2022	SS	WH



END A		END B	
A	1	1	B
B	1	1	A
A	2	2	B
B	2	2	A
A	3	3	B
B	3	3	A



NOTES:

- 1 MAX. CONNECTOR ATTENUATION 0.3dB, MEASURED AT 1310 nm AND 1550 nm ACCORDING TO IEC 61300-3-4 INSERTION METHOD B
- 2 MIN. RETURN LOSS 50 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 1310 nm AND 1550 nm
- 3 INFORMATION ON LABEL, SEE DETAIL FOR EXAMPLE.
- 4 THE TAIL SEAL BETWEEN OUTER SHELL AND INNER BODY CAN MEET IP65 REQUIREMENT
- 5 CABLE INFORMATION:
 - CORE DIAMETER: 9/125um
 - OUTER JACKET DIAMETER: Ø5.8MM
 - OUTER JACKET COLOUR: BLACK
 - OUTER JACKET MATERIAL: LSZH
 - CABLE ATTENUATION:0.4dB/km @1310 nm OR 0.3dB/km @1550 nm
 - UL1666 & CPR: Dca-s2,d1,a1 COMPLIANCE
- 6 THE TRANSITION DEVICE MEETS IP67



Qty	Description	Item
9	MARKER LABEL 1	9
L	Ø4.8MM PROTECTIVE TUBING, LSZH, BLACK	8
1	MARKER LABEL 2	7
L	Ø5.8MM FO CABLE 6FIBER, SINGLE MODE G657A2, LSZH, BLACK	6
1	CABLE BRANCHING DEVICE, 3C	5
1	CABLE BRANCHING DEVICE, 6C	4
L	FLEXIBLE PROTECTION TUBE, LSZH, BLACK O.D 2 to 2.5mm	3
3	FULLAXS LC DUPLEX PLUG ASSEMBLY, BLACK	2
3	LC DUPLEX CONNECTOR, SINGLE MODE, BLUE	1

Description		Item	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 20NOV2020 SIDDHARTH SINGH	
DIMENSIONS: mm		CHK 20NOV2020 HERBERT. ZHANG	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 20NOV2020 ROGER SONG	
0 PLC ± -		NAME FOSM 6F FULLAXS LC-LC DUPLEX	
1 PLC ± -		SIZE A2	
2 PLC ± -		CAGE CODE 00779	
3 PLC ± -		DRAWING NO C=2835697	
4 PLC ± -		RESTRICTED TO -	
ANGLES ± -		SCALE NTS	
MATERIAL -		SHEET 1 of 2	
FINISH -		REV A1	
WEIGHT -		CUSTOMER DRAWING	



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-

LENGTH "L" IN MM	TOLERANCE
L ≤ 50000	±1%
L > 50000	±1%

PART NUMBER 	DESCRIPTION	 LENGTH (Meters)	REMARKS
1-2835697-0	FOSM 6F FULLAXS LC-LC DUPLEX,10m	10±0.10	
2-2835697-0	FOSM 6F FULLAXS LC-LC DUPLEX,20m	20±0.20	
3-2835697-0	FOSM 6F FULLAXS LC-LC DUPLEX,30m	30±0.30	
5-2835697-0	FOSM 6F FULLAXS LC-LC DUPLEX,50m	50±0.50	
7-2835697-0	FOSM 6F FULLAXS LC-LC DUPLEX,70m	70±0.70	
9-2835697-9	FOSM 6F FULLAXS LC-LC DUPLEX,100m	100±1.0	
9-2835697-8	FOSM 6F FULLAXS LC-LC DUPLEX,150m	150±1.5	
9-2835697-6	FOSM 6F FULLAXS LC-LC DUPLEX,250m	250±2.5	

2835697

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SIDDHARTH SINGH 20NOV2020	 TE Connectivity	
		CHK HERBERT. ZHANG 20NOV2020		
		APVD ROGER SONG 20NOV2020	NAME FOSM 6F FULLAXS LC-LC DUPLEX	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC	
MATERIAL		FINISH	WEIGHT	RESTRICTED TO
			A2 00779	
			C=2835697	
		CUSTOMER DRAWING	SCALE NTS	SHEET 2 OF 2
			REV A1	