




7-13PIN



3-6PIN



2PIN



7-11, 13P侧面图

12P侧面图

■ SPECIFICATIONS

- Voltage rating: 250V AC/DC
- Current rating: 3.0A, AC/DC
- Withstanding Voltage: 1000VAC/minute
- Insulation resistance: 1,000MΩ min
- Temperature range: -40°C to +105°C
- Contact resistance: 20mΩ max

■ WAFER

- Part No: CS-1001-XXA (LOCK)
- Poles: 2-13
- Material: PA66 A63V0 UL 94V-0 .
- Q' TY: 500 pcs/PE Bag

NO	PART NO	DIMENSION (mm)			
	Top entry type	A	B	C	D
2	CS-1001-02A (LOCK)	7.5	6.10	2.50	0.85
3	CS-1001-03A (LOCK)	10.00	8.60	5.00	2.1
4	CS-1001-04A (LOCK)	12.50	11.10	7.50	4.3
5	CS-1001-05A (LOCK)	15.00	13.60	10.00	6.9
6	CS-1001-06A (LOCK)	17.50	16.10	12.50	9.4
7	CS-1001-07A (LOCK)	20.00	18.60	15.00	2
8	CS-1001-08A (LOCK)	22.50	21.10	17.50	2
9	CS-1001-09A (LOCK)	25.00	23.60	20.00	2
10	CS-1001-10A (LOCK)	27.50	26.10	22.50	2
11	CS-1001-11A (LOCK)	30.00	28.60	25.00	2
12	CS-1001-12A (LOCK)	32.50	31.10	27.50	2
13	CS-1001-13A (LOCK)	35.00	33.60	30.00	2

RoHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	HOUSING	品名	CS-1001-XXA (LOCK)	X.	±0.50	材料		单位	mm	SHEET 1 OF 1				
版本	A/0	设计	李文畅	X.X	±0.40	颜色	白色	比例	1:1	▲	修改内容	修改日期		
制定部门	工程部	绘制	李文畅	X.XX	±0.30	画法		数量		▲				
工程图号	CST-1001	审核	CHENMINGBING	X.XXX	±0.20	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.						▲		
制定日期	2018/12/30	核准	CUIMIN	X.XXXX	±0.10							▲		