

# P1CA-SAFRPUFP-U137-6.5

Cable Assembly, Reverse Polarity SMA Bulkhead Female to U.FL Right Angle Plug, 1.37 mm cable, 6.5 inch (165 mm).

## Product Features

P1CA-SAFRPUFP-U137-6.5 is a 50 Ohm flexible cable assembly, SMA Female Bulkhead Reverse Polarity to U.FL plug right angle. The cable diameter is 1.37mm and the assembly is 6.5 inch (165 mm).



## Electrical Specification: T<sub>Ambient</sub> = 25° C

| Parameter       | Frequency Range | Units | Min | Typical | Max | Notes |
|-----------------|-----------------|-------|-----|---------|-----|-------|
| Frequency Range |                 | GHz   | DC  |         | 6.0 |       |

## Mechanical And Environmental Specifications:

| Parameter       | Description                | Notes |
|-----------------|----------------------------|-------|
| Connector 1     | SMA Female                 |       |
| Connector 2     | U.FL Male                  |       |
| Coax Cable      | Flex, Ultra Small Diameter |       |
| Cable Type      | 1.37 mm                    |       |
| Length          | 6.5                        |       |
| RoHS Compliance | Yes                        |       |

## Product Notes