

Hospital-Grade Power Cord, NEMA 5-15P to C13 - Green Dot, 13A, 125V, 16 AWG, 3 ft. (0.91 m), Clear Plugs

MODEL NUMBER: P006-003-HG13CL



Connects your PC, mobile cart or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

Features

Hospital-Grade Power Cable is a Safe Solution for Medical Facilities This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

Designed and Tested to Strict Hospital-Grade Standards Both fully molded ends are clear, so you can inspect their internal connections at a glance. This hospital-grade power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

Specifications

OVERVIEW	
UPC Code	037332193247
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125

Highlights

- Fully molded clear plugs allow visual inspection of internal construction to ensure safety
- Recommended for connecting devices to power outlets outside patient-care vicinities
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- Hospital-grade power cord replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet

Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 3 ft. away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P006-003-HG13CL Hospital-Grade Power Cord, NEMA 5-15P to C13, 3 ft., Clear Plugs

PHYSICAL	
Plug Color	Clear
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	7.00 x 9.90 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 25.15 x 1.27
Shipping Weight (lbs.)	0.35
Shipping Weight (kg)	0.16
ENVIRONMENTAL	
Operating Temperature Range	-4° to 221°F (-20° to 105°C)
Storage Temperature Range	-4° to 221°F (-20° to 105°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed

Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty