





INK MARKING <FP2046> :YFC CAT6A UTP 10 GIGABIT ETHERNET PATCH CABLE ISO/IEC 11801 & EN 50288
& ANSI/TIA-568.2-D & IEC 332.1 ▲ 24AWGX4P TYPE CMX(UL) E164469-XX

Operation Temperature:-20°C~+60°C

conductor resistance:92↓(Ω/Km) at 20°C



L(ft)	T(inch)	T(%)	L(ft)	T(inch)	T(%)
0.5	±0.6	10%	15	±3.15	1.75%
1	±1.2	10%	20	±4	1.67%
1.5	±1.2	6.67%	25	±4	1.33%
2	±1.2	5%	30	±6	1.67%
3	±1.2	3.33%	35	±6	1.43%
4	±1.2	2.5%	40	±6	1.25%
5	±1.2	2%	50	±6	1.0%
6	±1.2	1.67%	75	±6	0.67%
7	±2	2.38%	100	±6	0.5%
8	±2	2.08%	125	±6	0.4%
9	±2	1.85%	150	±6	0.33%
10	±2	1.67%	175	±6	0.29%
12	±2	1.39%	200	±6	0.25%

CABLEMAX

③	MOLD	PVC YU-02	A/R	Kg
②	PLUG	8P8C 50U RJ45	2	PCS
①	CABLE	CAT.6A UTP PVC 24AWG*4P BC	A/R	M
NO.	PART NAME	SPECIFICATION DESCRIPTION	QT'Y	UNIT


Drawn By:	Date: 10 / 31 / 2022	Description: Cat.6A UTP Cables
Checked By:	Sheet 1 of 2	Model No. CM-1007XXXXBSTK
Approved By:	Scale 1:1	Rev. 01 Unit: mm

NOTE: CARTON MATERIAL MUST BE A=A


Cable Part No. Color Guide *Replace "XX" in the Part No. to the respective color code (e.x. CM-100751GNBSTK for a Green cable)

White = WT Gray = GY Black = BK Blue = BL Green = GN Purple = PU Yellow = YW Orange = OR Red = RD


Front



Back



PE BAG SIZE(INCH)	PART NO.	length/FT	CARION SIZE(INCH)	Q'TY	G.W(LBS)
6.89x7.48	CM-100751XXBSTK	1	15.75x15.75x9.06	300	25.65
6.89x7.48	CM-100752XXBSTK	2	15.75x15.75x9.06	300	23.11
6.89x9.06	CM-100753XXBSTK	3	15.75x15.75x7.87	120	18.48
6.89x9.06	CM-100754XXBSTK	4	15.75x15.75x9.06	120	22.66
6.89x9.06	CM-100755XXBSTK	5	15.75x15.75x7.87	100	22.44
7.87x9.45	CM-100756XXBSTK	6	15.75x15.75x6.69	80	21.12
7.87x9.45	CM-100757XXBSTK	7	15.75x15.75x7.87	80	23.98
7.87x9.45	CM-100758XXBSTK	10	15.75x15.75x9.06	80	32.56
9.25x10.63	CM-100759XXBSTK	15	15.75x15.75x7.87	40	24.22
9.25x10.63	CM-100760XXBSTK	20	15.75x15.75x7.87	30	23.76
9.25x10.63	CM-100761XXBSTK	25	15.75x15.75x9.06	25	28.86
9.25x10.63	CM-100762XXBSTK	35	18.11x11.81x10.63	30	38.94
9.25x10.63	CM-100762XXBSTK	35	16.54x16.54x9.84	30	38.94
9.25x11.81	CM-100763XXBSTK	50	15.75x15.75x9.84	20	37.18
9.25x11.81	CM-100764XXBSTK	75	18.50x17.13x9.84	20	52.36



CABLEMAX

Drawn By:	Date: 10 / 31 / 2022	Description: Cat.6A UTP Cables
Checked By:	Sheet 2 of 2	Model No. CM-1007XXXXBSTK
Approved By:	Scale 1:1	Rev. 01 Unit: mm 