



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Wire Size: .14 mm²

Outside Cable Diameter: 1 mm [.039 in]

Shielded: No

Cable Assembly Length: .3 m [.98 ft]

Features

Product Type Features

Connector Type (End A)	Socket Housing
Connector Type (End B)	Socket Housing
Cable Style	Discrete Pairs

Configuration Features

Number of Positions	4
---------------------	---

Electrical Characteristics

Impedance	100 Ω
-----------	-------

Body Features

Cable Color	Gray
Cable Flammability Rating	VW-1

Contact Features

Contact Mating Area Plating Material	Gold (Au)
--------------------------------------	-----------

Mechanical Attachment

Mating Alignment	With
------------------	------



Housing Features

Housing Material	LCP
------------------	-----

Dimensions

Wire Size	.14 mm²
Outside Cable Diameter	1 mm [.039 in]

Operation/Application

Shielded	No
----------	----

Other

Cable Assembly Configuration	Double Ended
Cable Assembly Length	.3 m [.98 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 214012-E
SRCA 1,27 4 M 1 SMD 137 E1 094 * GURT *

TE Part # 284697-E
SRCP 1,27 4 M 1 SMD 137 E1 094 * GU-H *

TE Part # 839164-E
IDCCS SRC 1,27 10 * SFX SFX 300 PVC

TE Part # 839178-E
IDCCS SRC 1,27 12 * SFX AFU 200 PVC

TE Part # 384979-E
SRCA 1,27 4 M 1 SMD 137 E1 105 * GURT *

Also in the Series | ERNI MiniBridge

PCB Headers & Receptacles(81)

Pluggable I/O Cable Assemblies(20)

Wire-to-Board Connector Assemblies & Housings(1)

Customers Also Bought

TE Part #DTM04-4P-E004
DEUTSCH DTM Housings

TE Part #102241-4
06 MODIV HSG COMP SR .100 POL

TE Part #121397P024
ES2000-NO.3-B8-0-STK

TE Part #2176163-2
UPF50 0.1% 5PPM 100R

TE Part #5677962007
RNF-3000-39/13-X-STK

TE Part #1337810-2
50 OHM COAX SMA STR PLUG ELB P

TE Part #86016-5
MOD IV RECP LP

TE Part #1060-20-0222
PIN, SF, SIZE 20, 16-22, NI/NI

839018-E

4 Positions, .98 ft [.3 m], Gray Cable, 26 AWG, .14 mm², Discrete Pairs, Socket Housing, Socket Housing, VW-1, 1 mm [.039 in] Diameter



Documents

Product Drawings

IDCCS SRC 1,27 4 * SFX SFX 300 PVC

English

CAD Files

Customer View Model

ENG_CVM_CVM_839018-E_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_839018-E_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_839018-E_1.3d_stp.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Datasheet - ERNI MiniBridge 1.27mm Connectors

Datasheet - ERNI MiniBridge 1.27mm Connectors

English

Datasheet - ERNI MiniBridge 1.27mm Connectors

German