



Product: [6300FE](#)

Security & Sound, 2 Conductor 18 AWG, BC, Shielded, CMP

Product Description

Security & Commercial Audio Cable, Plenum-CMP, 2-18 AWG stranded bare copper conductors with Flamarrest® insulation, Beldfoil® shield and Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Noisy Environment
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	18 AWG	7x26	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.009 in (0.23 mm)	0.063 in (1.6 mm)	Black, Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.162 in (4.11 mm)	Yes

Overall Cable Diameter (Nominal):	0.162 in (4.11 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	6.4 Ohm/1000ft	70 pF/ft (230 pF/m)	126 pF/ft (413 pF/m)	14 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	0°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
1.6 in (41 mm)	1.6 in (41 mm)

Max. Pull Tension:	50.3 lbs (22.8 kg)
Bulk Cable Weight:	21 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	5300FH

History

Update and Revision:	Revision Number: 0.524 Revision Date: 04-13-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
6300FE 010Z500	Black	ReelTuff Box	500 ft		
6300FE 010U1000	Black	UnReel	1,000 ft	612825423201	
6300FE 010I1000	Black	Reel	1,000 ft	612825174721	
6300FE 010Z1000	Black	ReelTuff Box	1,000 ft	612825174752	
6300FE D15I1000	Blue	Reel	1,000 ft	612825174776	
6300FE 008U1000	Gray	UnReel	1,000 ft	612825423188	
6300FE 008Z1000	Gray	ReelTuff Box	1,000 ft	612825350613	
6300FE 005I1000	Green, Dark	Reel	1,000 ft	612825350606	
6300FE 877500	Natural	Reel	500 ft	612825174738	
6300FE 877U500	Natural	UnReel	500 ft	612825423218	
6300FE 877I1000	Natural	Reel	1,000 ft	612825174769	C
6300FE 877U1000	Natural	UnReel	1,000 ft	612825174745	
6300FE 877Z1000	Natural	ReelTuff Box	1,000 ft	612825350699	
6300FE 002I1000	Red	Reel	1,000 ft	612825350576	
6300FE 007I1000	Violet	Reel	1,000 ft	612825174684	
6300FE 009U250	White	UnReel	250 ft	612825174714	
6300FE 009U500	White	UnReel	500 ft	612825423195	
6300FE 009U1000	White	UnReel	1,000 ft	612825174707	
6300FE 009I1000	White	Reel	1,000 ft	612825174691	
6300FE 009Z1000	White	ReelTuff Box	1,000 ft	612825350620	
6300FE 004I1000	Yellow	Reel	1,000 ft	612825350583	

© 2023 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.