




Product: [8778MN](#)

SpaceMaker™, 6 Pr #22 Str TC, PO Ins, IS/OS, PVC Jkt, AWM 2937



Request Sample

Product Description

SpaceMaker™, 6 Pair 22AWG (19x34) Tinned Copper, PO Insulation, Individual & Overall Beldfoil® Shield, PVC Outer Jacket, AWM 2937

Technical Specifications

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	6	22 AWG	19x34	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.010 in (0.25 mm)	0.050 in (1.3 mm)	Black & White, Red & Green, Brown & Blue, Orange & Yellow, Purple & Gray, Pink & Tan

Inner Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (19x36) TC

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (19x34) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.016 in (0.41 mm)	0.317 in	Yes

Overall Cable Diameter (Nominal): 0.317 in

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
18.1 Ohm/1000ft	33 pF/ft (110 pF/m)	81.6 pF/ft (268 pF/m)	4.2 Amps per Conductor at 30°C

Voltage

UL Voltage Rating

300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-20°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
1.272 in (32.31 mm)	1.272 in

Max. Pull Tension:	129.4 lbs (58.69 kg)
Bulk Cable Weight:	61 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	FT2
AWM Compliance:	AWM 2937
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.309 Revision Date: 05-05-2023
----------------------	--

Part Numbers

Variants

Item #	Color	UPC
8778MN 006100	Blue, Light	612825385936
8778MN 0061000	Blue, Light	612825385943
8778MN 008100	Gray	612825385950
8778MN 0081000	Gray	612825382683
8778MN 004100	Yellow	612825385912
8778MN 0041000	Yellow	612825385929

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.