





- NOTES:
- 1." "DENOTES CRITICAL DIMENSIONS
 - 2.Part name:Outlet
 - 3.Power Rating: 15A 250VAC
 - 4.Life test:No Load condition: 5,000 cycles
 - 5.On Load test:
 - (a) Tested at Over Load condition 150% rated current: 500 cycles.
Check temp rise - not exceed 30°C
 - (b) Tested at On Load condition - rated current 15A: 500 cycles.
Check temp rise - not exceed 30°C
 - 6.Terminal pull force 10kg(min)
 - 7.Insertion Force:9±4kg
 - 8.Withdrawal Force:6±3kg

电话: 0769-82310511-867
邮箱: hooya89@hooya.hk

Part name : Female 4-Poles Connector

2	BODY	PBT 4130(a) 94-V0 Gray Blue E304813	1
1	PIN 1#	C2680 4.8X0.8 Tin-plating 3~5µm	4
NO.	PART NAME	MATERIAL	Q'TY

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE			simon	SCALE	NO			
3	→	8	→	X	±0.4				MAT'L	***			
2	→	7	→	X.X	±0.3				MATERIAL NO.		DRAWING NO.	REV.	
1	修改进胶口	6	→	X.XX	±0.2				RT-C05C-C		WIF111007	B	
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°	LEGION ELECTRONIC & HARDWARE CO.,LTD							