


NOTES:


- 1.Circuit: ON/OFF
- 2.Operation force(Waterproof cap removal): $500 \pm 200\text{gf}$
- 3.Electrical rating: 8A 250VAC (ULCUL CQC)
15A 125VAC (ULCUL CQC)
12(6)A 250VAC (ENEC17)
- 4.Contact resistance: $<30\text{m}\Omega$
5. Insulation resistance: $>100\text{M}\Omega$
(500VDC between open contacts)
- 6.Dielectric strength: $>1500\text{V}$ 1 minute
- 7.Color: cover is red, body is black.
- 8.Comply with the requitements of the EU directive 2002/95/EC RoHs and subsequent amendments.
- 9.Life:The switch can satisfy the test standard of BPT0001 and life requirement of all the products.
- 10.Terminal:#187 TAB Terminal,accord the UL310 standard.
- 11.Satisfy the test requirement of PST-11,switch impact.
- 12.Waterproof cap Material PVC GM5075, Yellow card:E96789
- 13.UL file NO:E300970.
- 14.Waterproof cap hardness: $40^{\circ} \pm 10^{\circ}$.
- 15.Glue the waterproof and the switch together. And be sure the waterproof does not shed when tension strength less than 3KG.
- 16.Change to low lead material.







电话 : 0769-82210511-867

邮箱 : hooya89@hooya.hk


V : hooya89



Panel cut out(Thickness: $1.54 \pm 0.1\text{mm}$)



Circuit of Switch



	→		→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM			
	→		→	RANGE	TOLERANCE				LMC	SCALE	FIT			
	→		→	X	±0.3					MAT'L	***			
	改用低铅材料 2020.11.25		→	X.X	±0.2					MATERIAL NO.		DRAWING NO.	REV	
	增加备注		→	X.XX	±0.1	LEGION ELECTRONIC & HARDWARE CO.,LTD					RT-S02-117-R4NBRC DC		WIF111003	C
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°									