


NOTES:





- 1.Circuit: ON/OFF
- 2.Operation force: $500 \pm 200\text{gf}$
- 3.Electrical rating: 8A 250VAC ULCUL CQC
15A 125VAC ULCUL CQC
12(6)A 250VAC ENEC
- 4.Contact resistance: $<50\text{m}\Omega$
- 5.Insulation resistance: $>100\text{M}\Omega$
(500VDC between open contacts)
- 6.Dielectric strength: $>1500\text{V}$ 1 minute
- 7.Color: cover is black(red), body is black.

电话: 0769-82310511-867
邮箱: hooya89@hooya.hk

Panel cut out(Thickness: 3mm Max)



Circuit of Switch



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC 2021.09.22	SCALE	NO		
3	→	8	→	X	±0.30					MAT'L	***		
2	安规刻字修改 2021. 11. 25	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	加强筋修改 2021. 11. 25	6	→	X.XX	±0.10	LEGION ELECTRONIC & HARDWARE CO., LTD.				RT-S02-117-A1NBR	WIF121058	A1	
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°								