

NOTES:

- 1.Circuit: Reset OFF
- 2.Operation farce: $800\pm300\text{gf}$
- 3.Electrical rating: 10(4)A 250V~ VDE
10A 125V~ UL CUL CQC
6A 250V~ UL CUL CQC
- 4.Contact resistance: $<50\text{m}\Omega$
- 5.Insulation resistance: $>100\text{M}\Omega$ (500VDC
between open contacts)
- 6.Dielectric strength: $>1500\text{VAC}$ 0.5mA 1 mintute
- 7.Color: cover is black, body is black.


电话 : 0769-82310511-867

邮箱 : hooya89@hooya.hk







V : hooya89

Panel cut - out:

X	Dim.Y	Dim.Z
0.75~1.25mm	$19.20+0.1/-0$	$12.80+0.1/-0$
1.25~2.0mm	$19.30+0.1/-0$	$12.80+0.1/-0$



Circuit of Switch



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				simon 2010.11.07	SCALE	FIT		
3	→	8	→	X	±0.4					MAT'L	***		
2	→	7	→	X.X	±0.3					MATERIAL NO.		DRAWING NO.	REV
1	500 → 800 2020. 07. 08	6	→	X.XX	±0.2					RT-S01-147-L17NB1B		WIF120035	A1
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°	LEGION ELECTRONIC & HARDWARE CO.,LTD							

4

3

2

1