




NOTES:

- 1.Rating : 16A GP 125/250VAC 5E4 40T125
16(4)A 125/250VAC 5E4 40T125
16A 42VDC 5E4 40T125
- 2.Contact resistance : 50mΩ Max
- 3.Insulation resistance : >100MΩ (Min) 500VDC
- 4.Dielectric strength : >1500VAC 0.5mA 1 minutes



电话: 0769-82310511-867

邮箱: hooya89@hooya.hk

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM				
4	→	9	→	RANGE	TOLERANCE				LMC 2019.05.20	SCALE	NO			DRAWING NO.	REV.
3	→	8	→	X	±0.30					MAT'L	***				
2	→	7	→	X.X	±0.20					MATERIAL NO.					
1	→	6	→	X.XX	±0.10					RT-M1-0C3B16C200		WIF119088	A0		
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.									