

ATGBICS AL4518003-E6 Avaya-Nortel Compatible Direct Attach
Twinax Cable, 10GBase-CX CX4 to CX4 (3m, Passive)

Brand : ATGBICS

Product code: AL4518003-E6-C

Product name : AL4518003-E6 Avaya-Nortel Compatible
Direct Attach Twinax Cable, 10GBase-CX CX4 to CX4 (3m,
Passive)



AL4518003-E6 Avaya-Nortel Compatible Direct Attach Twinax Cable, 10GBase-CX CX4 to CX4 (3m,
Passive)

ATGBICS AL4518003-E6 Avaya-Nortel Compatible Direct Attach Twinax Cable, 10GBase-CX CX4 to CX4
(3m, Passive):

ATGBICS AL4518003-E6 compatible 10GBase-CX CX4 to CX4 direct attach cable operates over passive copper with a cable length of 3m. Our product meets the specification of Avaya-Nortel AL4518003-E6= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards and protocols. ATGBICS AL4518003-E6 Avaya-Nortel Compatible Direct Attach Twinax Cable, 10GBase-CX CX4 to CX4 (3m, Passive). Cable length: 3 m, Connector 1: CX4, Connector 2: CX4, Data transfer rate: 10000 Mbit/s



Features		Features	
Product colour *	Black	Country of origin	United Kingdom
Cable length *	3 m	Operational conditions	
Connector 1 *	CX4	Operating temperature (T-T)	0 - 70 °C
Connector 2 *	CX4	Storage temperature (T-T)	-40 - 80 °C
Connector 1 gender *	Male	Operating relative humidity (H-H)	10 - 90%
Connector 2 gender *	Male	Storage relative humidity (H-H)	10 - 85%
Jacket material	Polyvinyl chloride (PVC)	Packaging data	
Conductor material	Copper	Quantity per pack	1 pc(s)
Ethernet interface type	10 Gigabit Ethernet	Technical details	
Networking standards	IEEE 802.3ae	Sustainability compliance	✓
AWG wire size	30	Sustainability certificates	RoHS
Data transfer rate	10000 Mbit/s	Doesn't contain	Lead
Plug and Play	✓		
Certification	CE, FCC, RoHS		



5056468725332

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 21-SEP-2023. Prints or copies of Information are only valid on the printed Publication date