







- 1.Rating : 2.5A 250VAC UL CUL
- 2.Contact resistance : 50mΩ Max
- 3.Insulation resistance : >100MΩ Min 500VDC
- 4.Dielectric strength : >2000VAC 0.5mA 1 minutes



5				DIMENSIONAL
4				RANGE
3				X
2				X.X
1	取消北欧四国和3C安规	刘美昌	2011. 04. 11	X.XX
NO	DESCRIPTION	APPROVED	DATE	ANGLES

5	→			DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM				
4	→			RANGE	TOLERANCE				LMC 2017.06.08	SCALE	FIT				
3	→			X	±0.3					MAT'L	***				
2	→			X.X	±0.2					MATERIAL NO.				DRAWING NO.	REV.
1	→	取消北欧四国和3C安规	刘美昌	2011.04.11	X.XX					±0.1	RT-C06-A1B-FC			*****	A1
NO	DESCRIPTION		APPROVED	DATE	ANGLES	LEGION ELECTRONIC & HARDWARE CO.,LTD									

电话：0769-82310511-867
邮箱：hooya89@hooya.hk
V：hooya89

LEGION ELECTRONIC & HARDWARE CO., LTD