





NOTES:

- 1.Circuit:ON/OFF
- 2.Operation force:500±200gf
- 3.Electrical rating:15A 125VAC
8A 250VAC
12(6)A 250V~
- 4.Contact resistance:<30mΩ
- 5.Insulation resistance:>1000MΩ(500VDC
between open contacts)
- 6.Dielectric strength:>1500Vac 0.5mA 1 minute
- 7.Color: cover is black of fog, body is black.
- 8.Comply with the requirements of the EU directive 2002/95/EC RoHS and subsequent amendments.
- 9.Life:The switch can satisfy the test standard of BPT0001 and life requirement of all the products.
- 10.Terminal:#187 TAB Terminal,accord the UL310 standard.
- 11.Satisfy the test requirement of PST-11,switch impact.
- 12.UL file NO:E300970
- 13.Waterproof cap Material PVC GM5075,
△ Yellow card:E96789
- 14.Waterproof cap hardness:40°±10°


Panel cut out(Thickness: 1.54±0.1)



fog is black faced



Marking:




Mark

Date code
week year

电话: 0769-82310511-867
邮箱: hooya89@hooya.hk
V: hooya89

Circuit of Switch



	→		→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		DRAWING NO.	REV
	→		→	RANGE	TOLERANCE				SIMON	SCALE	FIT			
	增加说明		→	X	±0.4					MAT'L	***			
	Mark		→	X.X	±0.3					MATERIAL NO.				
	ENEC取代VDE10年12月執行		→	X.XX	±0.2									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°					LEGION ELECTRONIC & HARDWARE CO.,LTD				

SIMON

LEGION ELECTRONIC & HARDWARE CO.,LTD.

RT-S02-117-R4NBB3C DC

WIF110002

B