

10GBase CX4 Cable, 3M (10-ft.)

MODEL NUMBER: N263-03M



Highlights

- Works with any Manufacturers' 10Gb XenPak
- Made with Premium Madison TurboTwin cable
- Compliant with the IEEE Draft specification P802.3ak/D5.3

System Requirements

- Ethernet switches with CX4 / Xenpak modules for 10Gbps linking

Package Includes

- 10 GBase CX4 Cable - 3 Meter

Description

Tripp Lite's high-speed 10Gbps CX4 cables provide an ultra high performance, cost effective solution for Gigabit Copper applications. Featuring 30AWG Madison TurboTwin twinaxial cable, these cables utilize up to 3.125 gigabytes per second wire speed connections with four channels. Cables work with any manufacturers' 10Gbps Xenpak transceiver that utilize the Ejector style latch connector. Tripp Lite CX4 cables are available in 0.5 meter, 1 meter, and 3 meter lengths.

Features

- Flexible 30AWG Madison TurboTwin Cable
- Ejector style latch mechanism
- Connects the CX4 modules between two switches
- Fully 802.3ak compliant
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332138514
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	9.8
Cable Length (m)	2.99
Cable Length (in.)	117.6

Shipping Dimensions (hwd / in.)	10.00 x 12.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 30.48 x 1.27
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
CONNECTIONS	
Side A - Connector 1	CX4 [SFF-8470] (MALE)
Side B - Connector 1	CX4 [SFF-8470] (MALE)
Angled Connector	No
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty