






NOTES:

- 1.Circuit: ON/OFF
- 2.Operation force: $550 \pm 150\text{gf}$ (without waterproof)
 $1000 \pm 500\text{gf}$ (waterproof)
- 3.Electrical rating: 8A 250VAC ULCUL CQC
15A 125VAC ULCUL CQC
12(6)A 250VAC ENEC
- 4.Contact resistance: $<30\text{m}\Omega$
- 5.Insulation resistance: $>100\text{M}\Omega$
(500VDC between open contacts)
- 6.Dielectric strength: $>1500\text{V}$ 1 minute
- 7.Color: cover is red, body is black.
- 8."○"Denotes critical dimensions.



Panel cut out (Thickness: 3mm Max)



Circuit of Switch



电话 : 0769-82310511-867
邮箱 : hooya89@hooya.hk
V : hooya89



53-0020-141-401

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM			
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	FIT			
3	→	8	→	X	±0.3					MAT'L	***			
2	→	7	→	X.X	±0.2					MATERIAL NO.			DRAWING NO.	REV
1	→	6	→	X.XX	±0.1									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°	LEGION ELECTRONIC & HARDWARE CO.,LTD				RT-S02-117-R4NBR2C DC		WIF119045	A	