



4.Dielectric strength : >2000VAC 0.5mA 1 minutes

邮箱: hooya89@hooya.hk



3	BODY	PA66 UL94V-0	Black & White	1
2	1# terminal	C2680	1/2H Tin-plating 3~5 μm	2
1	1# PIN	C3602	Ni-plating 3~5 μm	2
NO.	PART NAME	MATERIAL		Q'TY

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC 2019.05.20	SCALE	NO		
3	→	8	→	X	±0.30					MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.10					RT-C08-G2-*J		WIF122021	AO
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO.,LTD							