


电话 : 0769-82310511-867
邮箱 : hooya89@hooya.hk
V: hooya89



NOTES:

1. Rating: 10A 125/250VAC
2. CONTACT RESISTANCE: 50mΩ Max
3. INSULATION RESISTANCE: 100MΩ Min, at 500VDC
4. WITHSTAND VOLTAGE: 2000VAC 0.5mA 1 minute

品 名	X. X
RT-C14B-D08-13-R	0.8mm
RT-C14B-D10-13-R	1.0mm
RT-C14B-D12-13-R	1.2mm
RT-C14B-D15-13-R	1.5mm
RT-C14B-D20-13-R	2.0mm
RT-C14B-D30-13-R	3.0mm

8	本体	PA66	1
7	盖子	PA66	1
6	3#端子	C2680 1/2H Ag-plating	2
5	3#PIN	C1100 1/2H Ag-plating	2
4	连接片	C2680 1/2H Tin-plating	1
3	2#PIN	C2680 1/2H Ni-plating	2
2	1#PIN	C2680 1/2H Ni-plating	1
1	1#端子	C2680 1/2H Tin-plating	3
NO.	PART NAME	MATERIAL	Q' TY

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2019.05.20	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.			
1	增加1.2面板厚度 20200330	6	→	X.XX	±0.10							DRAWING NO.	REV.
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.				RT-C14B-D20-13-R		WIF119052	A1