






NOTES:

- 1.Circuit:ON/OFF
- 2.Operation force:500±200
- 3.Electrical rating:15A 125VAC
8A 250VAC
12(6)A 250V~
- 4.Contact resistance:<30mΩ
- 5.Insulation resistance:>1000MΩ(500VDC
between open contacts)
- 6.Dielectric strength:>1500V 1 minute
- 7.Color: cover is black, body is black.
- 8.Waterproof cap Material PVC GM5075,
Yellow card:E96789
- 9.Waterproof cap hardness:40°±10°



Panel cut out(Thickness: 3mm Max)



Circuit of Switch



电话 : 0769-82310511-867
邮箱 : hooya89@hooya.hk
V : hooya89



	→		→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM				
	→		→	RANGE	TOLERANCE				LMC	SCALE	FIT			DRAWING NO.	REV
	→		→	X	±0.4					MAT'L	***				
	增加说明		→	X.X	±0.3					MATERIAL NO.		RT-S02-117-C DC	WIF108016	B1	
	取消VDE		→	X.XX	±0.2										
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°	LEGION ELECTRONIC & HARDWARE CO.,LTD									