



NOTES:





- 1.Circuit:Reset OFF 
- 2.Operation farce: $800\pm 300\text{gf}$
- 3.Electrocal rating:10(4)A 250V~
10A 125V~
6A 250V~
- 4.Contact resistance: $<30\text{m}\Omega$
- 5.Insulation resistance: $>100\text{M}\Omega$ (500VDC
between open contacts)
- 6.Dielectric strength: $>1500\text{VAC}$ 0.5mA 1 mintute
- 7.Color: cover is black, body is black.

Panel cut - out:












| X | Dim.Y | Dim.Z |
|-------------|----------------|----------------|
| 0.75~1.25mm | $19.20+0.1/-0$ | $12.80+0.1/-0$ |
| 1.25~2.0mm | $19.30+0.1/-0$ | $12.80+0.1/-0$ |



Circuit of Switch



电话 : 0769-82310511-867
邮箱 : hooya89@hooya.hk
V : hooya89

| | | | | | | | | | | | | | | |
|---|-------------|---|-------------|------------------------|-----------|---------------------------------------|---------|--------|-------|-------------------|-------|---|-------------|-----|
|  | → |  | → | DIMENSIONAL TOLERANCES | | APPROVED | CHECKED | DESIGN | DRAWN | ALL SIZE ARE IN | MM |  | | |
|  | → |  | → | RANGE | TOLERANCE | | | | | SCALE | FIT | | | |
|  | → |  | → | X | ±0.4 | | | | | MAT'L | *** | | | |
|  | → |  | → | X.X | ±0.3 | | | | | MATERIAL NO. | | | DRAWING NO. | REV |
|  | 500 → 800 |  | → | X.XX | ±0.2 | | | | | | | | | |
| NO | DESCRIPTION | NO | DESCRIPTION | ANGLES | ±0.5° | LEGION ELECTRONIC & HARDWARE CO., LTD | | | | RT-S01-145-L1NB1B | ***** | A | | |