

NOTES:

1.Circuit:ON/OFF

2.Electrical rating:10A 125VAC

6A 250VAC

10(4)A 250VAC

3.Contact resistance:<30mΩ (intital)


4.Insulation resistance:>1000MΩ(500VDC)
between open contacts)

5.Dielectric strength:>1500V/1 minute


6.Color: cover is White, body is White

Panel cut - out:

X	Dim.Y	Dim.Z
0.75~1.25mm	19.20+0.1/-0	12.80+0.1/-0
1.25~2.0mm	19.30+0.1/-0	12.80+0.1/-0








Circuit of Switch



电话: 0769-82310511-867

邮箱: hooya89@hooya.hk



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				管林华	SCALE	FIT		
3	→	8	→	X	±0.4				2018.6.1	MAT'L	***	DRAWING NO.	REV
2	→	7	→	X.X	±0.3					MATERIAL NO.		RT-S01-113-L4NWW	WIF106027
1	→	6	→	X.XX	±0.2								B
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±0.5°	LEGION ELECTRONIC & HARDWARE CO.,LTD							