







DIAGRAM



Socket : RT-C14-M0B-AA

1.Rating : 10A 250VAC VDE CCC
15A 250VAC UL CUL

2.Insulation resistance : >100MΩ Min 500VDC

3.Dielectric strength : >2000VAC 1 minute

Switch : SS21-BBIWF-S4-R

1.Rating : 10A 125/250VAC UL CUL

12(4)A 250V~ ENEC17;NEMKO;CQC;KC

2.Contact resistance : <50mΩ

3.Insulation resistance : >100MΩ (500VDC between open contacts)

4.Dielectric strength : >1500VAC 0.5mA 1 minute

电话：0769-82310511-867

邮箱：hooya89@hooya.hk

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		DRAWING NO.	REV.
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO			
3	→	8	→	X	±0.30				2020.11.14	MAT'L	***			
2	→	7	→	X.X	±0.20					MATERIAL NO.				
1	→	6	→	X.XX	±0.10					RT-C14-N1+SS21-6BB		*****		A0
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.								