






4 3 2 1



PANEL CUT-OUT



品 名		X. X
RT-C14B-D1+SS11-1BB	0. 8mm	
RT-C14B-D2+SS11-1BB	1. 0mm	
RT-C14B-D3+SS11-1BB	1. 5mm	
RT-C14B-D4+SS11-1BB	2. 0mm	
RT-C14B-D5+SS11-1BB	3. 0mm	
RT-C14B-D6+SS11-1BB	1. 2mm	

- Socket: RT-C14B-D**-13-R
- 1.Rating: 10A 250VAC (CCC; UL; CUL)
 - 2.Insulation resistance: >100MΩ Min 500VDC
 - 3.Withstand voltage: >2000VAC 0.5mA 1 minute
- Switch: SS11-BBIWG-R20-R
- 1.Rating: 16A 125/250VAC (UL; CUL)
16(4)A 250V~ (ENEC17; NEMKO; CQC)
 - 2.Contact resistance: <50mΩ
 - 3.Insulation resistance: >100MΩ Min 500VDC
 - 4.Dielectric strength: >1500VAC 0.5mA 1 minute

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2020.12.23	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.10					RT-C14B-D*+SS11-1BB		WIF121023	A0
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.							

4 3 2 1