




NOTES:

1. Rating : 16A GP 125/250VAC 5E4 40T125
16(4)A 125/250VAC 5E4 40T125
16A 42VDC 5E4 40T125
2. Contact resistance : 50mΩ Max
3. Insulation resistance : >100MΩ (Min) 500VDC
4. Dielectric strength : >1500VAC 0.5mA 1 minutes



电话: 0769-82310511-867

邮箱: hooya89@hooya.hk

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN			DRAWING NO. REV.		
4	→	9	→	RANGE	TOLERANCE					MM					
3	→	8	→	X	±0.30					SCALE					NO
2	→	7	→	X.X	±0.20					MAT'L					***
1	→	6	→	X.XX	±0.10					MATERIAL NO.					
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.				RT-M1-0C3B16B200		*****		A	
LMC 2019.05.20															