

4


3

2

1

D

D



C


C

B

B

A

A



电话: 0769-82310511-867
邮箱: hooya89@hooya.hk

Socket : RT-C14B-H00-13-R

1.Rating : 10A 250VAC (CCC ; UL ; CUL)

2.Insulation resistance : >100MΩ Min 500VDC

3.Withstand voltage : >2000VAC 0.5mA 1 minute

Switch : SS21-BBIWG-R

1.Rating : 10A 125VAC 6A 250VAC (UL ; CUL ; CQC)

10(4)A 250V~ (VDE)

2.Contact resistance : <50mΩ

3.Insulation resistance : >100MΩ Min 500VDC

4.Dielectric strength : >1500VAC 0.5mA 1 minute

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		DRAWING NO.	REV.
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO			
3	→	8	→	X	±0.15				2019.09.12	MAT'L	***			
2	→	7	→	X.X	±0.10					MATERIAL NO.				
1	→	6	→	X.XX	±0.05									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.				RT-C14B-H1+SS21-1BB		*****		A0

4

3

2

1