

Heavy-Duty PDU Power Cord, C13 to Right-Angle C14 - 15A, 250V, 14 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P005-010-14RA



Computer power extension cord with right-angle C14 plug allows connection of a PC, printer or monitor in tight spaces or awkward angles.

Features

C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Right-Angle C14 Plug Makes Connecting in Tight Spaces Easier The C13 to C14 right-angle cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled C14 plug guides the computer power supply cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

Highlights

- Right-angle C14 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering computers, servers and other network devices
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 10-ft. (3.05 m) away in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source away from your workstation
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

Package Includes

- P005-010-14RA C13 to Right-Angle C14 Power Cable, 10-ft. (3.05 m), Black

Specifications

OVERVIEW	
UPC Code	037332179951
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250

PHYSICAL	
Color	Black
Power Cord Jacket Type	SJT
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	1.03
Shipping Weight (kg)	0.47
ENVIRONMENTAL	
Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14 - RIGHT ANGLE
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
High Voltage	Yes
Locking Plug	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty