


NOTES:




- 1.Circuit: ON/ON
- 2.Operation force: $500 \pm 200\text{gf}$
- 3.Electrical rating: 8A 250VAC ULCUL CQC
15A 125VAC ULCUL CQC
12(6)A 250VAC ENEC
- 4.Contact resistance: $<50\text{m}\Omega$
- 5.Insulation resistance: $>100\text{M}\Omega$
(500VDC between open contacts)
- 6.Dielectric strength: $>1500\text{V}$ 1 minute
- 7.Color: cover is black, body is black.

电话 : 0769-82310511-867
邮箱 : hooya89@hooya.hk
V : hooya89





Panel cut out(Thickness: 3mm Max)



Circuit of Switch



雾面黑色上盖



09	转轴	NICKEL PALTED BRASS	1pcs
08	接触片	C2680 1/2H Ag-plate	1pcs
07	本體	PA66	1pcs
06	上蓋	PA66	1pcs
05	動接點	Ag Clad Copper Alloy	2pcs
04	靜接點	Ag Clad Copper Alloy	2pcs
03	端子	C2680 1/2H Ag-plate	1pcs
02	端子	C2680 1/2H Ag-plate	2pcs
01	彈簧	SWC	1pcs
NO.	Name	Material	Q' ty

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		MM		
4	→	9	→	RANGE	TOLERANCE					SCALE		FIT		
3	→	8	→	X	±0.4					MAT'L		***		
2	→	7	→	X.X	±0.3					MATERIAL NO.		DRAWING NO.	REV	
1	→	6	→	X.XX	±0.2									
NO DESCRIPTION		NO DESCRIPTION		ANGLES	±0.5°	LEGION ELECTRONIC & HARDWARE CO.,LTD				RT-S02-127-R1NBB		WIF121050		A

管林华
17.11.13