





RoHS Compliant



-USB-4PIN SOLDER TAIL
焊线式

特性: Specifications:

电器 Electrical:

接触阻抗:Contact Resistance
30milliohms MAX

耐电压:Dielectric Withstanding Voltage:
50V AC AT sea LeveL

绝缘阻抗:Insulation Resistance:
100MEGA ohms MIN

材料:Material:

塑胶:PBT

耐高温塑胶

端子:Contact:Copper Alloy 铜合金

铁壳:Shell: SPCC-SD 铁

电镀:Finish:

端子:Contact: Piated Gold in Mating Area;

Tin/Lead On Solder Talls

接触点镀金0.5u'/1u'/3u',脚镀锡

铁壳:Shell:

Tin/Lead Plating 镀镍

<i>C</i>	塑胶内部条线由两条改为一条	21.11.1
<i>B</i>	塑胶地线侧减胶	20.08.1
<i>A</i>	NEW ISSUE	18.05.2
版本 REV.	设 变 内 容 MODIFICATION	日 期 DATE

单位	MM	* Inspection Item	HJ-Tech	东莞市捷捷通讯科技有限公司
比例	1:1	① Cp/Cpk and SPK	手机: 15015262131	手机: 13714786106
張數	1/1	TOLERANCE UNLESS OTHERWISE SPECIFIED	圖號	2LS00P0015
制图	LUA	.X±0.25 .X±.3"	名稱	USB-A工短体大电流
審核		.XX±0.20 .X±.1"	TITLE	20mm大电流铁壳短路
		.XXX±0.10 .XX±"	角法	
				成品圖