


电话 : 0769-82310511-867  
 邮箱 : hooya89@hooya.hk  
 V : hooya89



NOTES:  
 1. Rating: 10A 125/250VAC 15A 125/250VAC  
 2. CONTACT RESISTANCE: 50mΩ Max  
 3. INSULATION RESISTANCE: 100MΩ Min, at 500VDC  
 4. WITHSTAND VOLTAGE: 2000VAC 0.5mA 1 minute

8	本体	PA66	1
7	盖子	PA66	1
6	3#端子	C2680 1/2H Ag-plating	2
5	3#PIN	C1100 1/2H Ag-plating	2
4	连接片	C2680 1/2H Tin-plating	1
3	2#PIN	C2680 1/2H Ni-plating	2
2	1#PIN	C2680 1/2H Ni-plating	1
1	1#端子	C2680 1/2H Tin-plating	3
NO.	PART NAME	MATERIAL	Q'TY

△5	→	△10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	
△4	→	△9	→	RANGE	TOLERANCE				LMC	SCALE	NO	
△3	→	△8	→	X	±0.4				2018. 11. 13	MAT'L	***	
△2	→	△7	→	X.X	±0.3					MATERIAL NO.	DRAWING NO.	REV.
△1	→	△6	→	X.XX	±0.2					RT-C14B-G00-13-R	WIF119093	A
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD						

4

3

2

1