




# NOTES:

- 1.Rating : 2.5A 250VAC (CCC VDE)  
2.5A 250VAC 7A 125VAC (UL CUL)
- 2.Contact resistance : 50mΩ Max
- 3.Insulation resistance : >100MΩ (Min) 500VDC
- 4.Dielectric strength : >2000VAC 0.5mA 1 minutes

电话: 0769-82310511-867

邮箱: hooya89@hooya.hk

|     |             |                              |      |
|-----|-------------|------------------------------|------|
| 3   | BODY        | PA66 94-V0 Black             | 1    |
| 2   | 1# terminal | C2680 1/2H Tin-plating 3~5um | 2    |
| 1   | 1# PIN      | C3602 Ni-plating 3~5um       | 2    |
| NO. | PART NAME   | MATERIAL                     | Q'TY |

| NO | DESCRIPTION | NO | DESCRIPTION | DIMENSIONAL TOLERANCES | APPROVED | CHECKED | DESIGN | DRAWN | ALL SIZE ARE IN | MM  | DRAWING NO. | REV. |
|----|-------------|----|-------------|------------------------|----------|---------|--------|-------|-----------------|-----|-------------|------|
| 5  | →           | 10 | →           | RANGE                  |          |         |        |       | SCALE           | FIT |             |      |
| 4  | →           | 9  | →           | X                      |          |         |        |       | MAT'L           | *** |             |      |
| 3  | →           | 8  | →           | X.X                    |          |         |        |       | MATERIAL NO.    |     |             |      |
| 2  | →           | 7  | →           | X.XX                   |          |         |        |       |                 |     |             |      |
| 1  | →           | 6  | →           | ANGLES                 |          |         |        |       |                 |     |             |      |
|    |             |    |             |                        |          |         |        |       |                 |     |             |      |

ROCK TEK ELECTRONIC(SHENZHEN) CO.,LTD.

RT-C08-L0-BJ

\*\*\*\*\*

A0