









PANEL CUT-OUT



Socket : RT-C14-F0B-AA

1.Rating : 10A 250VAC VDE CCC
15A 250VAC UL CUL

2.Insulation resistance : >100MΩ Min 500VDC

3.Dielectric strength : >2000VAC 1 minute

Switch : SS21-BBIWG-R

1.Rating : 10A 125/250VAC UL CUL

12(4)A 250V~ ENEC17;NEMKO;CQC

2.Contact resistance : <50mΩ

3.Insulation resistance : >100MΩ (500VDC between open contacts)

4.Dielectric strength : >1500VAC 0.5mA 1 minute

电话：0769-82310511-867

邮箱：hooya89@hooya.hk

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC 2018.07.07	SCALE	FIT		
3	→	8	→	X	±0.3					MAT'L	***		
2	→	7	→	X.X	±0.2					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.1					RT-C14-F1+SS21-1 BB		WIF121016	A0
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°					ROCK TEK ELECTRONIC(SHENZHEN) CO.,LTD.			