

电话 : 0769-82310511-867
邮箱 : hooya89@hooya.hk
V : hooya89

SPECIFICAIONS:

RATING: 7A 14VDC

CONTACT RESISTANCE: 50m Ω (Max)





INSULATION RESISTANCE: DC500V 1 MINUTE

OPERATING FORCE: 600 $\pm$ 200g

LIFE CYCLE: 10,000CYCLES

The circuit display sequential two sorts case when you press sequentail the key.

<1.>ON 1 & C
<2.>ON C & 2



5	→			DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→			RANGE	TOLERANCE					SCALE	FIT		
3	→			X	±0.30					MAT'L			
2	→			X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	→			X.XX	±0.10					RT-P02-2		WIF110013	A
NO	DESCRIPTION	APPROVED	DATE	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO.,LTD							